



# JAGA16 Millmax pin orientations

Aug 1, 2016

## JAGA16 pin orientations

We use a Millmax connector for input electrodes (2 x 9 pins, 0.05" spacing, MILL-MAX-852-10-100-10-001000 for male pins, 853-93-100-10-001000 for female pins). The digikey part numbers for those pins are ED83100-ND (straight male) and ED87100-ND (right angle male).

To determine the pin orientation:

1. Orient the pins by holding JAGA16 with the micro-USB port situated at the bottom right of the device.
2. Reference (REF) and Ground (GND) pins are found closest to the USB side.
3. Top row is odd numbered channels and the bottom row is even numbered channels.



